



Actual

Catalog Number: AL13/M16/C90/BL
Product ID: 7TCA296000R0195
EAN Number: 05020963013270
Status: Active

90 Degree Conduit Fitting, Fixed External Male Thread, Nominal Conduit Size 13mm, M16 Metric Thread, Polyamide (Nylon) 66 Plus Aluminium, Black

North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	Adaptaflex
Type	Conduit Fitting with Metric Threads
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit
Size	NC 13mm
Material	Polyamide/Nylon 6.6
Color	Black
Connection	90 Degree
Cable Entry	M16 Thread

European Specifications (ETIM)

ETIM	EC001176 Screw connection for corrugated plastic hose
Nominal diameter	13mm
Degree of protection (IP)	IP66
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Type of connection	Snap connection
Thread type	Metric
Thread connection size	M16 x 1.5
Thread length	11.5mm
Material	Polyamide
Colour	Black
Approved in combination with protective conduit UR	Y
Approved in combination with protective conduit DIN EN 61386-23	Y

Packaging

Inner Quantity	10
Outer Quantity	250
Outer Dimensions (inches)	1x1x1
Weight Uom	0.02 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
 www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com