



Representative

Catalog Number: BVTR-121212GT
Product ID: 7TAA292150R0354
UPC Number: 78620999473
EAN Number: 07630030229527
Status: Active

VT T-Piece for IP68GT Conduit - 3 X Conduit Sizes NW/Metric 12/16, Color Black

North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	PMA
Type	T-Connectors
Application	For Cable Protection Systems In a Wide Range of Applications
Size	NW12 x 3
Material	Polyamide 6
Insulation Class	IP68GT
Color	Black
Temperature Rating	-40 Degrees C to 105 Degrees C; Short Term to 160 Degrees C

European Specifications (ETIM)

ETIM	EC001172 Coupler for corrugated plastic hoses
Material	Plastic
Material quality	Polyamide (PA)
Operating temperature	-40 - +105°C
Degree of protection (IP)	Other
Model	T-piece
Nominal size	16-16mm
Colour	Black

Packaging

Inner Quantity	20
Inner Dimensions (inches)	15.74x11.81x4
Outer Quantity	200
Outer Dimensions (inches)	15.748x11.811x8.661
Weight Uom	0.12 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com