



## Thin-Wall Heat-Shrinkable Tubing

**T&B Catalog Number:**

CPO375-S-C

**UPC Number:**

78620959076

**Status:**

Active

**Description:**

Heat Shrink Tubing, Striped, 3/8 Inch, Length 100 Foot

### Features

Flame-retardant, cross-linked polyolefin.

Meets UL 224, 125°C; CSA 22.2 No. 198.1, 125°C;  
MIL-DTL-23053/5 Class 1&2; AMS 3636 & 3637;  
DEF STAN 59-97, Issue 3, Type 2a

### General

Style	CPO Series Non-Lined
Color	Green/Yellow Striped
Temperature Range	-55°C - 135°C
Shrink Ratio	2:1

### Dimension Information

Length (feet)	100
Minimum Expanded I.D. (inches)	0.375
Maximum Recovered I.D. (inches)	0.187
Nominal Recovered Wall (inches)	0.025
Cable Range	12 - 6 AWG

### Specifications

Shrink Temperature	120°C
--------------------	-------

### Packaging

Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	2.6 lbs. Each

### Application Support

Specifications	Available on Website
Overview	Available on Website

### Notes

Order multiple is for 4 ft. sticks is 25 sticks. Order multiple for reels is 1 reel. When ordering standard package, order by package not feet.

UL Recognized File Number E137759 and CSA Certified. Clear material not UL Recognized.

Larger diameters available upon special request; consult Customer Service.

### Certifications



**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: techsupport@tnb.com