



PRINT

Catalog Number: F.66.12SW
Product ID: 7TAA292910R0033
UPC Number: 78620995651
EAN Number: 7630030238932
Status: Active

Black Braided Hose, (F66) Material - Polyamide 6,6, Conduit Size NW - 12

Family

Where To Buy

Zip Code:

Quantity:

[Buy Online](#)

- High temperature stability
- Self extinguishing UL 94 V2
- Free from halogens
- Rail
- Industry, aviation, construction of vehicles and trains
- For bundling and protection of electrical wires and cables

SUBMITTAL PACKAGE

- North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Brand Name	PMA
Type	Braided Hose
Application	Machine
Trade Size	NW12
Length	50 m
Flexibility	Medium
Material	Polyamide/Nylon 6.6
Color	Black

- European Specifications (ETIM)

ETIM	EC001182 Braided hose
Nominal diameter	12mm
Bundle diameter	11-16mm
Material	Plastic
Material quality	Polyamide (PA)
Halogen free	Y
Surface protection	Untreated
Colour	Black
Open (mountable afterwards)	N
Temperature	-55 - +125°C
Fire resistance in accordance with UL94	V2
Approved according to UR	Y
Approved according to DIN 5510	Y
Approved according to NF F 16-101	Y

- Packaging

Inner Quantity	1
Outer Quantity	4
Outer Dimensions (inches)	15.748x11.811x7.874
Weight Uom	0.01 lbs. Each

Where To Buy