



Actual

Catalog Number: MPNY-750-0-D
Product ID: 7TAG054850R0003
UPC Number: 72849407422
EAN Number: 05414363031727
Status: Active

Cable Tie Mounting Base, Black Nylon 6.6 for Temperatures up to 70 Degrees Celsius (158 F), Length of 18.79mm (0.74 Inch), Width of 18.79mm (0.74 Inch), Height of 5.08mm (0.20 Inch), Mechanical Strength 40 Newtons (9 Pounds), Synthetic Rubber Adhesive Mounting Method, 500 Pack

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Brand Name	Catamount
Type	3/4 x 3/4 Mount
Material	Nylon/Polyamide 6.6
Color	Black
Screw Holes	#4
Mounting	Adhesive
Operating Temperature	-40 Degree F to 185 Degree F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	18.79mm
Width	18.79mm
Height	5.08mm
Type of fastening	Self-adhesive
Material	Plastic
Material quality	Polyamide PA
Colour	Black

Packaging

Inner Quantity	500
Inner Dimensions (inches)	13x7x1
Outer Quantity	10000
Outer Dimensions (inches)	20x11.7x10
Weight Uom	1.25 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US	WSD-001485
-----------------------------------	------------

For further technical assistance, please contact us...

ABB Installation Products - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com