



Representative



PRINT

Catalog Number: NC25/50M
Product ID: 7TCA298000R0251
EAN Number: 5020963023064
Status: Active

Standard Weight, General Purpose Conduit, NC Size 25/NW Size 22, Outside Diameter 25.6mm, Inside Diameter 21.3mm, Static Bend Radius 40mm, High Flexibility and Fatigue Life, IP40 Rating, Polyamide 6, Reel Length 50 Meters, Black

Where To BuyZip Code: Quantity: [Buy Online](#)

CAD



SUBMITTAL

PACKAGE

[+ North American Specifications \(UNSPSC\)](#)[+ European Specifications \(ETIM\)](#)[+ Packaging](#)**HOME**[Report Issue](#)**LOGIN**[T&B Access \(Dist only\)](#)[My Toolbox](#)**RESOURCES**[Catalog PDFs](#)[End User Toolkit](#)[Solution Set Brochures](#)[Vertical Market](#)[Brochures](#)[Where To Buy](#)**SUPPORT**[Contact Us](#)[Global Locations](#)[Product Support](#)[Tool Services](#)[Legal/Privacy](#)**COMPANY**[Careers](#)[News](#)

© ABB Installation Products Inc.