



PRINT

**Ring Terminal**

**T&B Catalog Number:** F10731  
**UPC Number:** 78621082968  
**Status:** Active

**Description:**  
Non-Insulated Tubular Ring Terminal, Length 1.42 Inches, Width .62 Inches, Bolt Hole 3/8 Inch, Wire Range 4/4AN, Copper, Tin Plated



ROHS SUBMITTAL PACKAGE

**Where To Buy**

Enter Zip Code:

Enter Quantity:

**Features**

- These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indentor or double indentor (recommended for solid wire).

**General**

Insulation Type	Non-Insulated - Tubular
Terminal Series	F
Material	Copper
Finish	Electro -Tin Plated
Color	Metallic
Wire Range	4
Stud Size	3/8

**Dimension Information**

Stock Thickness	.04
A (inches)	1.42
B (inches)	.62
C (inches)	.34
M (inches)	1.08

**Specifications**

Temperature Rating	150°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0
ML Specification	MS-20659-112

**Tooling**

Tool Charts	<a href="#">Click Here</a>
Application Tools	<a href="#">WT115A, TBM6, TBM6S, WT3185</a>
Recommended Tool	<a href="#">ERG4008</a>

**Packaging**

Order Multiple	100
Inner Package	100
Outer Package	1000
Package Type	Standard
Package Height	3.2
Package Length	3.6
Package Width	3.1
T&B Sold in UOM	Each
T&B Weight Per UOM	1.5 lbs. per 100

**Application Support**

T&B Sales Drawings	<a href="#">wsd-000168</a>
Overview	<a href="#">Click Here</a>
Wire Guide Tables	<a href="#">Click Here</a>

**Notes**

- Not available on Mylar Tape.

**Certifications**

RoHS Compliance [Yes](#) [Generate Compliance Certificate](#)

**Certifications**



File Nbr:  
E9809