



T&B[®]

Wire Connectors & Termination
T&B Catalog Number:

UPC Number: 10-401
 78378600476
Status: Active
Description:

High temperature Porcelain Wire Connector, HI-1.

Features

Three sizes accommodate #18-14AWG stranded Copper
 300 Volt rated.

Application

For high temperature applications over 105 degree C

General

Wire Range #18-14
 Minimum 2 #18
 Maximum 1 #18 w/2 #16

Dimension Information

Dimension A (inches) 11/16
 Dimension B (inches) 13/32
 Dimension C (inches) 3/16
 Dimension D (inches) 1/4

Packaging

T&B Order Multiple 100
 Package in Units 100
 T&B Sold in UOM Each
 T&B Weight Per UOM 0.38 lbs. per 100

Application Support

Product Overview Available on Website

Notes

Wire range size applies to stranded only.

Certifications

RoHS Compliance Yes

Certifications



File Nbr:
 E 9809

For further technical assistance, please contact us...

