



## Wire Connectors & Termination

### T&B Catalog Number:

10-407

### UPC Number:

78378600475

### Status:

Active

### Description:

High temperature Porcelain Wire Connector, HI-7.

### Features

Three sizes accommodate #18-14AWG stranded Copper  
300 Volt rated.

### Application

For high temperature applications over 105 degree C

### General

Wire Range #18-14

Minimum 2 #18

Maximum 4 #16

### Dimension Information

Dimension A (inches) 27/32

Dimension B (inches) 17/32

Dimension C (inches) 7/32

Dimension D (inches) 13/32

### Packaging

T&B Order Multiple 100

Package in Units 100

T&B Sold in UOM Each

T&B Weight Per UOM 0.75 lbs. per 100

### Application Support

Product Overview Available on Website

### Notes

Wire range size applies to stranded only.

### Certifications

RoHS Compliance Yes

### Certifications



File Nbr:

E 9809