



Representative

**Catalog Number:** 256-30695-345  
**Product ID:** 7TAH007970R0181  
**UPC Number:** 78621064286  
**Status:** Active

Copper Two-Hole Lug, Standard Barrel, Peep Hole, Max 35kV, Wire Size 4/0 Weld 550/24, 3/8 Inch Bolt Size, 7/8 Inch Hole Spacing, Tin Plated, Die Color Code Yellow, Die Code 62

### North American Specifications (UNSPSC)

UNSPSC	39121405 Cable or wire lug
IGCC	4532 Cable or wire lug
Brand Name	Color-Keyed
Type	Standard Barrel
Standard	UL E9809
Cable Size	4/0 Weld
Stud Size	3/8 Inch
Number Of Holes	2
Voltage Rating	Max 35kV
Insulation	None
Material	Copper
Color	Yellow

### European Specifications (ETIM)

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	Straight
Slender flange model	N
Insulated	N
With sight-hole	Y
Material	Copper
Surface protection	Tinned
Number of fixing holes	2

### Packaging

Inner Quantity	10
Inner Dimensions (inches)	3.5x3x3
Outer Quantity	100
Outer Dimensions (inches)	16.4x7.8x3.5
Weight Uom	1.19 lbs. Each

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website

### For further technical assistance, please contact us...

ABB Installation Products - USA  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

ABB Installation Products Technical Support  
 MS 3B-50  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)