

PRODUCT-DETAILS

2920-TB

1/2 IN RANGER CORD CONN .125-.375



General Information

Extended Product Type	2920-TB
Product ID	7TBD105170R0006
EAN	5415022527797
Catalog Description	1/2 IN RANGER CORD CONN .125-.375
Long Description	Liquidtight Strain Relief Connector, 1/2 Inch, Straight, Cord Range 0.125 to 0.375 Inch, Throat Diameter 9/16 Inch, Steel Body, Glandnut, and Grip, Rubber Bushing

Additional Information

Product Main Type	T&B CORD AND CABLE FITTINGS
Application	A Liquidtight Fitting to Secure Flexible Cord or Power Cable to a Box or Enclosure and Provide Strain Relief
Product Type	Cord Connectors-Straight

Ordering

EAN	5415022527797
UPC	786210357898

Technical

Number of Batteries	0
---------------------	---

Color	Metallic
Size	1/2 inch

Container Information

Package Level 1 Units	25 piece
Package Level 1 Height	3 in 76 mm
Package Level 1 Depth / Length	5 in 127 mm
Package Level 1 Width	4.5 in 114 mm

Certificates and Declarations

Data Sheet, Technical Information	2920-TB
Instructions and Manuals	2920-TB

Classifications

UNSPSC	39121431
--------	----------

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

