



Actual

Catalog Number: 32517
Product ID: 7TAH006040R0101
UPC Number: 78621032517
EAN Number: 05415022246308
Status: Active

Locktite Copper Two-Way for Conductor Range 500-750 kcmil

- Easy installation. High conductivity. Wide cable range.
- Cables held by saddle and tightened by screws. Built-in lockwashers.

North American Specifications (UNSPSC)

| | |
|--------------------------------|---|
| UNSPSC | 39121408 Mechanical connectors |
| IGCC | 4541 Mechanical connectors |
| Brand Name | Blackburn |
| Type | Locktite Connectors |
| Special Features | Easy installation. High conductivity. Wide cable range. |
| Standard | UL E9809 |
| Material | Copper |
| Conductor Range (Main/Primary) | 500-750 kcmil |

Packaging

| | |
|---------------------------|------------------|
| Inner Quantity | 1 |
| Inner Dimensions (inches) | 3.3x2.8x2.3 |
| Outer Quantity | 5 |
| Outer Dimensions (inches) | 7.8x7.1x4.2 |
| Weight Uom | 141 lbs. per 100 |

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com