

Two-Piece Grounding Connectors and Dies for the Hexagonal Range

Stay grounded with easy-to-install connectors!
Connector Inner and Outer Sleeves



Non-Insulated Inner Sleeve — Cat. GSB



Non-Insulated Outer Sleeve — Cat. GSC

- Hard bronze inner sleeve is installed under braid
- Length 5/16"
- Tin plated per MIL-T-10727A
- Soft bronze outer sleeve slips over the braid and ground wire
- Length 1/4"
- Tin plated per MIL-T-10727A

CAT. NO.	COLOR CODE	I.D. (IN.)	O.D. (IN.)	MILITARY SPEC. NO.	STD PKG.	TOOLS		MILITARY SPEC. NO.	STD. PKG.				
						DIE NOS. FOR WT440/WT540*	DIE NOS. FOR 11901A						
Inner Sleeves						Outer Sleeves							
GSB046	Gray	.046	.075	21981-046	1,000	GSC101	Gray	.101	.124	4419	11989	21980-101	1,000
GSB058	Yellow	.058	.083	21981-058	1,000	GSC128	Blue	.128	.152	4400	11970	21980-128	1,000
GSB063	Red	.063	.088	21981-063	1,000	GSC149	Purple	.149	.179	4401	11971	21980-149	1,000
GSB071	Green	.071	.096	21981-071	1,000	GSC156	Yellow	.156	.193	4402	11972	21980-156	1,000
GSB080	Blue	.080	.103	21981-080	1,000	GSC175	Blue	.175	.215	4403	11973	21980-175	1,000
GSB090	Orange	.090	.113	21981-090	1,000	GSC187	Orange	.187	.227	4406	11976	21980-187	1,000
GSB096	Purple	.096	.119	21981-096	1,000	GSC194	Red	.194	.226	4406	11976	21980-194	1,000
GSB101	Yellow	.101	.124	21981-101	1,000	GSC199	Gray	.199	.235	4406	11976	21980-199	1,000
GSB109	Red	.109	.131	21981-109	1,000	GSC205	Yellow	.205	.245	4408	11978	21980-205	1,000
GSB115	Gray	.115	.146	21981-115	1,000	GSC219	Green	.219	.250	4408	11978	21980-219	1,000
GSB124	Green	.124	.145	21981-124	1,000	GSC225	Purple	.225	.256	4409	11979	21980-225	1,000
GSB128	Gray	.128	.152	21981-128	1,000	GSC232	Orange	.232	.263	4410	11980	21980-232	1,000
GSB134	Orange	.134	.156	21981-134	1,000	GSC261	Yellow	.261	.297	4411	11981	21980-261	1,000
GSB149	Blue	.149	.179	21981-149	1,000	GSC275	Gray	.275	.306	4412	11982	21980-275	1,000
GSB156	Red	.156	.193	21981-156	1,000	GSC281	Purple	.281	.331	4414	11984	21980-281	1,000
GSB165	Gray	.165	.194	21981-165	1,000	GSC287	Blue	.287	.327	4414	11984	21980-287	1,000
GSB175	Green	.175	.215	21981-175	1,000	GSC297	Green	.297	.335	4414	11984	21980-297	1,000
GSB187	Yellow	.187	.227	21981-187	1,000	GSC312	Yellow	.312	.362	4415	11985	21980-312	1,000
GSB194	Blue	.194	.226	21981-194	1,000	GSC327	Gray	.327	.372	4416	11986	21980-327	1,000
GSB205	Orange	.205	.245	21981-205	1,000	GSC348	Orange	.348	.393	4417	11987	21980-348	1,000
GSB219	Gray	.219	.250	21981-219	1,000	GSC359	Purple	.359	.399	5450	—	21980-359	1,000
GSB225	Yellow	.225	.256	21981-225	1,000	GSC375	Yellow	.375	.406	5451	—	21980-375	1,000
GSB232	Red	.232	.263	21981-232	1,000	GSC405	Red	.405	.453	5452	11988	21980-405	1,000
GSB250	Green	.250	.281	21981-250	1,000	GSC415	Blue	.415	.463	5452	11988	21980-415	1,000
GSB261	Blue	.261	.297	21981-261	1,000	GSC425	Gray	.425	.475	5454	—	—	1,000
GSB266	Gray	.266	.297	21981-266	1,000	GSC460	Gray	.460	.510	5456	—	21980-460	1,000
GSB275	Orange	.275	.306	21981-275	1,000	GSC500	Green	.500	.550	5457	—	21980-500	1,000
GSB281	Yellow	.281	.331	21981-281	1,000								
GSB287	Gray	.287	.327	21981-287	1,000								
GSB297	Red	.297	.335	21981-297	1,000								
GSB312	Purple	.312	.362	21981-312	1,000								
GSB348	Orange	.348	.400	21981-348	1,000								
GSB375	Blue	.375	.406	21981-375	1,000								

*Dies 4419 to 4417 are for WT440. Dies 5450 to 5457 are for WT540.
Order multiple is standard package

Order multiple is standard package