



Family

Catalog Number: 54207NT
Product ID: 7TAH007990R0623
UPC Number: 78620989202
Status: Active

Copper Two-Hole Lug, Standard Barrel Narrow Tongue Lug, Max 35kV, Wire Size #2-3 AWG, 1/4 Inch Bolt Size, 5/8 Inch Spacing, Tin Plated, Die Code 33, Die Color Code Brown

North American Specifications (UNSPSC)

UNSPSC	39121405 Cable or wire lug
IGCC	4532 Cable or wire lug
Brand Name	Color-Keyed
Type	Standard Barrel - Narrow Tongue
Standard	UL E9809
Cable Size	#2-3 AWG
Stud Size	1/4 Inch
Number Of Holes	2
Voltage Rating	Max 35kV
Insulation	None
Material	Copper
Color	Brown

European Specifications (ETIM)

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	Straight
Slender flange model	Y
Insulated	N
With sight-hole	N
Material	Copper
Surface protection	Tinned
Number of fixing holes	2

Packaging

Inner Quantity	25
Inner Dimensions (inches)	3.25x2.75x2.25
Outer Quantity	250
Outer Dimensions (inches)	12.18x6x3.31
Weight Uom	30 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000386
Technical Drawing / Data Sheet Canada	Available on Website

For further technical assistance, please contact us...

ABB Installation Products - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com