



Actual

Catalog Number: 54852BEUB
Product ID: 7TAH007820R0002
UPC Number: 78621059163
EAN Number: 05414363144274
Status: Active

Copper Two-Hole Lug, 90 Degree Bend Long Barrel, Blind End, Max 35kV, #6 AWG Wire, 1/4 Inch Bolt Size, 5/8 Inch Hole Spacing, Tin Plated, Die Code 24, Die Color Code Blue

North American Specifications (UNSPSC)

UNSPSC	39121405 Cable or wire lug
IGCC	4532 Cable or wire lug
Brand Name	Color-Keyed
Type	Long Barrel 90 Degree Bend
Standard	UL E9809
Cable Size	#6 AWG
Stud Size	1/4 Inch
Number Of Holes	2
Voltage Rating	Max 35kV
Insulation	None
Material	Copper
Color	Blue

European Specifications (ETIM)

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	90°
Slender flange model	N
Insulated	N
With sight-hole	N
Material	Copper
Surface protection	Tinned
Number of fixing holes	2

Packaging

Inner Quantity	50
Inner Dimensions (inches)	3.5x3x3
Outer Quantity	500
Outer Dimensions (inches)	16.5x7.5x3.5
Weight Uom	2.5 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-003166
Technical Drawing / Data Sheet Canada	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com