

Catalog Number: AB50-M50-90
Product ID: 7TCA298010R0083
EAN Number: 05020963053405
Status: Active

Sealed Conduit Fitting, 90 Degree Elbow, Compression Type, Conduit Size NC50/NW48, M50 Thread, Operating Temperature -40 to 120 Degrees Celsius, RoHS Compliant, IP67, 68 Rating, Very High UV Protection, Polyamide (Nylon), Black

North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	Harnessflex
Type	Sealed Conduit Compression Fitting
Special Features	Self Extinguishing, Low Smoke Toxicity, and Halogen Free
Application	Designed to Help Maintain System Integrity for Conduit Systems
Standard	ADR Approved (with NC conduits only) , RoHS
Size	Conduit Size NC50/NW48
Material	Polyamide/Nylon
Insulation Class	IP67, IP68
Color	Black
Connection	90 Degree, M50 Thread
Temperature Rating	-40 to 120 Degrees C

European Specifications (ETIM)

ETIM	EC001176 Screw connection for corrugated plastic hose
Nominal diameter	50mm
Nominal size in inch	1 1/2 inch
Degree of protection (IP)	IP68
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Type of connection	Thread
Thread type	Metric
Thread connection size	M50 x 1.5
Thread length	16mm
Material	Polyamide
Colour	Black

Packaging

Outer Quantity	2
Outer Dimensions (inches)	12x3x6
Weight Uom	0.24 lbs. Each

Header

3D Model	Available on Website
----------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
 www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com