



**Dual-Rated**  
**T&B Catalog Number:**

ADR11-32  
78378661006  
Active

**UPC Number:**  
**Status:**  
**Description:**

Type ADR-ALCUL Three-Conductor, Two-Hole Mount for Conductor Range Max 1/0 Str., Min 14 AWG

**Features**

Easy Installation - no special tools required.

**General**

Style	ALCUL Three-Conductor, Two-Hole Mount
Material	Aluminum
Plating	Tin-Plated
Conductor Range (AL or CU) Maximum	1/0 Str.
Conductor Range (AL or CU) Minimum	14 AWG

**Dimension Information**

Length (inches)	2 29/32
Width (inches)	1 15/16
Height (inches)	7/8
D (inches)	11/32
E (inches)	3/8
F (inches)	1/4
G (inches)	2 5/32
I (inches)	45/64

**Packaging**

T&B Inner Pack	6
Package in Units	60
T&B Sold in UOM	Each
T&B Weight Per UOM	22 lbs. per 100

**Application Support**

T&B Sales Drawings	wsd-001273
T&B Instruction Sheets	wsd-001273

**Notes**

NEMA spacing 1 inch centers.  
Connectors accomodating conductors 600 kcmil and larger have double rows of set screws (D suffix).  
UL 486B tested, AL9CU rated

**Certifications**

RoHS Compliance	Yes
-----------------	-----

**Certifications**



File Nbr:  
E9809

For further technical assistance, please contact us...

8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)