



Representative

Catalog Number: AL21/U138/C90/000620
Product ID: 7TCA296000R0731
EAN Number: 05020963028588
Status: Active

Connector Conduit Fitting, 90 Degree Elbow, Conduit Size 21, 1-3/8 Inch Connector UNEF Thread, Swivel Internal Thread, Black

North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	Adaptaflex
Type	Conduit Fitting with UNEF Threads
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit
Size	NC 21mm
Material	Polyamide/Nylon 6.6
Color	Black
Connection	90 Degree
Cable Entry	1-3/8 Inch UNEF Thread

European Specifications (ETIM)

ETIM	EC001176 Screw connection for corrugated plastic hose
Nominal diameter	21mm
Degree of protection (IP)	IP68
Model	90°-elbow
Revolving thread	Y
Construction type	Internal thread
Type of connection	Snap connection
Thread type	UNEF
Thread connection size	Other
Thread length	9.5mm
Material	Polyamide
Colour	Black
Approved in combination with protective conduit UR	N
Approved in combination with protective conduit DIN EN 61386-23	Y

Packaging

Outer Quantity	10
Outer Dimensions (inches)	1x1x1
Weight Uom	0.04 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
 www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com