



Representative

Catalog Number: AL28/M25/SFA/BL
Product ID: 7TCA296000R0828
EAN Number: 05020963033971
Status: Active

Straight Conduit Fitting, Swivel Internal Female Thread, Nominal Conduit Size 28mm, M25 Thread, Polyamide (Nylon) 66, Nickel Plated Brass Thread, Black

North American Specifications (UNSPSC)

| | |
|-------------|--------------------------------------------------------------------|
| UNSPSC | 39121311 Electrical fittings |
| IGCC | 4441 Electrical fittings |
| Brand Name | Adaptaflex |
| Type | Conduit Fitting with Metric Threads |
| Application | For Insertion into Threaded Entries or Knockout to Connect Conduit |
| Size | NC 28mm |
| Material | Polyamide/Nylon 6.6 |
| Color | Black |
| Connection | Straight |
| Cable Entry | M25 Thread |

European Specifications (ETIM)

| | |
|----------------------------------------------------|-------------------------------------------------------|
| ETIM | EC001176 Screw connection for corrugated plastic hose |
| Nominal diameter | 28mm |
| Degree of protection (IP) | IP66 |
| Model | Straight |
| Revolving thread | Y |
| Construction type | Internal thread |
| Type of connection | Snap connection |
| Thread type | Metric |
| Thread connection size | M25 x 1.5 |
| Thread length | 17mm |
| Total length | 34mm |
| Total height | 63.8mm |
| Material | Polyamide |
| Colour | Black |
| Approved in combination with protective conduit UR | Y |

Packaging

| | |
|---------------------------|----------------|
| Inner Quantity | 10 |
| Inner Dimensions (inches) | 1.8x2x2 |
| Outer Quantity | 10 |
| Outer Dimensions (inches) | 1.8x2x2 |
| Weight Uom | 0.14 lbs. Each |

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com