



Flexible Conduits & Fittings

T&B Catalog Number:

BFVD-171212GT

UPC Number:

78620994568

Status:

Active

Description:

PMAFIX one-piece black 'V' connector with universal safety clip. Material - polyamide 6, conduit size - 17, 12, 12.

Application

For cable protection systems in a wide range of applications

Characteristics

- Very high impact resistance
- Vibration-proof connection to PMAFLEX conduits
- Easy mounting, simple conduit push-in instruction
- High conduit pull-out strength
- Can be easily re-opened with a screwdriver
- Very good chemical properties
- Self-extinguishing, free from halogens and cadmium
- Fits both conduit profiles - fine (T) and coarse (G)

General

Material	Polyamide 6
Color	Black
Suitable for Use With	PMAFLEX, PMA Smart Line

Dimension Information

Fits to Conduit Size (NW)	17
Fits to Conduit Size (metric)	20
Fits to Conduit Size (inches)	1/2
Output fits to conduit size NW	12
Output fits to conduit size - Metric	16

Technical Information

Temperature Range-Continuous (Celsius)	-40 degree C - +105 degree C
Temperature-Short-Term (Celsius)	+160 degree C
Technical Data Sheet	Available on Website
Chemical Resistance Chart	Available on Website

Specifications

3dmodel	Available on Website
---------	----------------------

IP Ratings

IP Rating	IP66 stat. / IP54 dyn.
-----------	------------------------

Packaging

T&B Inner Pack	50
Package in Units	250
T&B Sold in UOM	Each
T&B Weight Per UOM	0.01 lbs. Each

Application Support

PMA Reference Guide	Available on Website
Product Overview-PMAFIX Connectors	Available on Website
	Available on Website

PMAFIX Connectors-Safety and Sealing
Systems

Certifications

RoHS Compliance Yes

Certifications



For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com