



Family

Catalog Number: BGI-M7556
Product ID: 7TAA292860R0009
UPC Number: 78620994592
EAN Number: 07630030208928
Status: A

GI Straight Nylon Connector, Female Thread - Thread M75x1.5, Fits to NW 56, Color Black

North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	PMA
Type	Straight Connector with Female Threads
Application	For Cable Protection Systems In a Wide Range of Applications
Size	NW56 ; M75 Thread
Material	Polyamide 6
Insulation Class	IP67
Color	Black

European Specifications (ETIM)

ETIM	EC001176 Screw connection for corrugated plastic hose
Nominal diameter	68mm
Degree of protection (IP)	IP50
Model	Straight
Revolving thread	N
Construction type	External thread
Type of connection	Snap connection
Thread type	Other
Thread connection size	Other
Thread material	Polyamide
Thread length	15mm
Total length	53.3mm
Material	Polyamide
Material sealing	No sealing
Colour	Black
Approved in combination with protective conduit CSA	N
Approved in combination with protective conduit UR	N
Approved in combination with protective conduit DIN EN 61386-23	N
Approved in combination with protective conduit Lloyd's Register	N
Operating temperature	-40 - +105°C

Packaging

Inner Quantity	10
Outer Quantity	30
Outer Dimensions (inches)	15.748x11.811x7.874
Weight Uom	0.01 lbs. Each

For further technical assistance, please contact us...

ABB Installation Products - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120

ABB Installation Products Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289

