

Accessories

System supports, half-shells



VH

VH

System support

- For applications in machine building and installation

Order No. Support ①	Order No. Clip ①	Order No. Complete ①	Fits to conduit size metric		Width x Height x Depth	Fixing screws
BVH-17-010	BVH-17-020	BVH-17-000	17	20	35 x 36 x 36 mm	6 x M5
BVH-23-010	BVH-23-020	BVH-23-000	23	25	35 x 44 x 36 mm	6 x M5
BVH-29-010	BVH-29-020	BVH-29-000	29	32	46 x 52 x 40 mm	6 x M5
BVH-36-010	BVH-36-020	BVH-36-000	36	40	53 x 58 x 60 mm	6 x M5
BVH-48-010	BVH-48-020	BVH-48-000	48	50	66 x 72 x 60 mm	6 x M5

- Optimal axial strain relief due to integrated rib
- Variable fixation possible due to six holes, safe against turning
- With safety lid suitable for overhead installation
- High retention forces

6



GN

GN

Half shell

- For conduit fixation in conjunction with beam systems, particularly in traction and machine applications

Order No. fine profile, black	Order No. coarse profile, black	Fits to conduit size metric		Outside \varnothing	Width
BGN-S12T	–	12	16	26.5 mm	34.0 mm
BGN-S17T	BGN-S17G	17	20	32.0 mm	34.0 mm
BGN-S23T	BGN-S23G	23	25	39.5 mm	34.0 mm
BGN-S29T	BGN-S29G	29	32	47.0 mm	34.0 mm
BGN-S36T	–	36	40	55.0 mm	36.5 mm
–	BGN-S36G	36	40	55.0 mm	34.0 mm
BGN-S48T	–	48	50	66.5 mm	36.5 mm
–	BGN-S48G	48	50	66.5 mm	34.0 mm
–	BGN-S70G	70	80	93.5 mm	38.0 mm

- Fixes conduit against axial movements
- Allows radial turning of conduit
- Especially suitable for dynamic applications due to rounded edges

① Please replace "B" for black with "S" for grey in front of the order no.