



Flexible Conduits & Fittings

T&B Catalog Number:

BVAD-N022GT

UPC Number:

78620994836

Status:

Active

Description:

PMAFIX 45 degree one-piece black elbow with universal safety clip. Material - polyamide 6, thread type - NPT, thread size - 3/8 in., conduit size NW - 12.

Application

For cable protection systems in a wide range of applications

Characteristics

- Very high impact resistance
- Vibration proof connection to PMAFLEX conduits
- Easy installation, simply push the conduit in
- High conduit pull-out strength
- Can be easily re-opened with a screwdriver
- Very good chemical properties
- Free from halogens and cadmium
- Fits both conduit profiles - Fine (T) and coarse (G)

General

Material	Polyamide 6
Color	Black
Thread Type	NPT
Compatible With	PMAFLEX, PMAFLEX Pro, PMA Smart Line

Dimension Information

Fits to Conduit Size (NW)	12
Fits to Conduit Size (metric)	16
Fits to Conduit Size (inches)	3/8
Thread Size (NPT)	1/2

Technical Information

Temperature Range-Continuous (Celsius)	-40 degree C to +105 degree C
Temperature-Short-Term (Celsius)	+160 degree C
Technical Data Sheet	Available on Website
Chemical Resistance Chart	Available on Website

Specifications

3dmodel	Available on Website
---------	----------------------

IP Ratings

IP Rating	IP66
-----------	------

Packaging

T&B Inner Pack	50
Package in Units	500
T&B Sold in UOM	Each
T&B Weight Per UOM	0.07 lbs. Each

Application Support

PMA Reference Guide	Available on Website
Product Overview-PMAFIX Connectors	Available on Website

Certifications

RoHS Compliance

Yes

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com