

Flexible Conduits & Fittings

T&B Catalog Number:

BVBV-M207

UPC Number:

78620994899

Status:

Active

Description:

PMAFIX 90 degree one-piece curved black elbow, material - polyamide 6. Thread type - metric, thread size - M20 x 1.5, conduit size NW - 17.



Application

For use in machine building and plant construction industries

Characteristics

Smooth elbow allows easy guidance through connector

Easy threading of wires and cables

Easy installation

High pull-out strength

Fits both conduit profiles - Fine (T) and coarse (G)

General

Material Polyamide 6

Color Black

Thread Type Metric

Compatible With PMAFLEX

Dimension Information

Fits to Conduit Size (NW) 17

Fits to Conduit Size (metric) 20

Fits to Conduit Size (inches) 1/2

Thread Size (Metric) M20 x 1.5

Technical Information

Temperature Range-Continuous (Celsius) -40 degree C to +105 degree C

Temperature-Short-Term (Celsius) +160 degree C

Technical Data Sheet Available on Website

Chemical Resistance Chart Available on Website

Specifications

3dmodel Available on Website

IP Ratings

IP Rating IP68 stat. / IP67 dyn.

Packaging

T&B Inner Pack 50

Package in Units 200

T&B Sold in UOM Each

T&B Weight Per UOM 0.04 lbs. Each

Application Support

PMA Reference Guide Available on Website

Product Overview-PMAFIX Connectors Available on Website

PMAFIX Connectors-Safety and Sealing Systems Available on Website

Systems

Certifications

RoHS Compliance Yes

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com