



Representative

**Catalog Number:** BVEMV-M638-14  
**Product ID:** 7TAA292330R0014  
**UPC Number:** 78620994928  
**EAN Number:** 07630030216992  
**Status:** Active

VEMV Connector, Metric Thread IP68 - Thread M63x1.5, Fits to NW/F.CK/F.CU 48/35/40, Thread Length 14.0mm, Color Black

### North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	PMA
Type	Connectors-Straight
Application	For Cable Protection Systems In a Wide Range of Applications
Size	NW48
Material	Polyamide 6 with Nickel Plated Aluminum Threads
Insulation Class	IP68
Color	Black
Connection	M63
Temperature Rating	-40 Degrees C to 105 Degrees C; Short Term to 160 Degrees C

### European Specifications (ETIM)

ETIM	EC001176 Screw connection for corrugated plastic hose
Nominal diameter	50mm
Degree of protection (IP)	IP68
Model	Straight
Revolving thread	N
Construction type	Internal thread
Type of connection	Snap connection
Thread type	Metric
Thread connection size	M63 x 1.5
Thread material	Other
Thread length	14mm
Total length	110mm
Material	Polyamide
Material sealing	Other
Colour	Black
Approved in combination with protective conduit CSA	N
Approved in combination with protective conduit UR	N
Approved in combination with protective conduit DIN EN 61386-23	N
Approved in combination with protective conduit Lloyd's Register	N
Operating temperature	-40 - +105°C

### Packaging

Inner Quantity	1
Outer Quantity	20
Outer Dimensions (inches)	15.748x11.811x7.874
Weight Uom	0.17 lbs. Each

### Header

3D Model

Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
860 Ridge Lake Blvd.  
Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
860 Ridge Lake Blvd.  
Memphis, TN 38120

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)