



Flexible Conduits & Fittings

T&B Catalog Number:

BVIRA-U152

UPC Number:

78620995018

Status:

Active

Description:

PMAFIX black female thread adapter with UNEF threads. Material - polyamide 6, thread size - 5/8 in. - 24, conduit size NW - 12.

Application

For use in machine, vehicle and traction building

Characteristics

Very high impact resistance

Suitable for the AMP connector series CPC

Vibration proof connection to PMAFLEX conduits

High conduit pull-out strength

Very good chemical properties

Free from halogens and cadmium

Fits both conduit profiles - Fine (T) and coarse (G)

General

Material Polyamide 6

Color Black

Thread Type UNEF

Compatible With PMAFLEX, AMP Connector series CPC

Dimension Information

Fits to Conduit Size (NW) 12

Fits to Conduit Size (metric) 16

Fits to Conduit Size (inches) 3/8

Thread Length (mm) 8.0

Thread Size (UNEF) 5/8" - 24

Connector Size (AMP) 11

Technical Information

Temperature Range-Continuous (Celsius) -40 degree C to +105 degree C

Temperature-Short-Term (Celsius) +160 degree C

Technical Data Sheet Available on Website

Chemical Resistance Chart Available on Website

Specifications

3dmodel Available on Website

IP Ratings

IP Rating IP68 stat. / IP67 dyn. On conduit side

Packaging

T&B Inner Pack 50

Package in Units 500

T&B Sold in UOM Each

T&B Weight Per UOM 0.09 lbs. Each

Application Support

PMA Reference Guide Available on Website

Product Overview-PMAFIX Connectors Available on Website

PMAFIX Connectors-Safety and Sealing Systems Available on Website

Certifications

RoHS Compliance Yes

Certifications



For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com