



Flexible Conduits & Fittings

T&B Catalog Number:

BVIR-M329

UPC Number:

78620995047

Status:

Active

Description:

PMAFIX black female thread adapter with metric threads. Material - polyamide 6, thread size - M32 x 1.5, nominal width/ conduit size - 29.

Application

For use in machine, vehicle and traction building

Characteristics

- Very high impact resistance
- Vibration-proof connection to PMAFLEX conduits
- High conduit pull-out strength
- Very good chemical properties
- Free from halogens and cadmium
- Fits both conduit profiles - Fine (T) and coarse (G)

General

Material	Polyamide 6
Color	Black
Thread Type	Metric
Suitable for Use With	PMAFLEX, PMA Smart Line

Dimension Information

Fits to Conduit Size (NW)	29
Fits to Conduit Size (metric)	32
Fits to Conduit Size (inches)	1
Thread Size (Metric)	M32 x 1.5

Technical Information

Temperature Range-Continuous (Celsius)	-40 degree C to +105 degree C
Temperature-Short-Term (Celsius)	+160 degree C
Technical Data Sheet	Available on Website
Chemical Resistance Chart	Available on Website

Specifications

3dmodel	Available on Website
---------	----------------------

IP Ratings

IP Rating	IP68 stat. / IP67 dyn. On conduit side
-----------	--

Packaging

T&B Inner Pack	20
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	0.09 lbs. Each

Application Support

PMA Reference Guide	Available on Website
Product Overview-PMAFIX Connectors	Available on Website
PMAFIX Connectors-Safety and Sealing Systems	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com