



Flexible Conduits & Fittings

T&B Catalog Number:

BVIVG-U436

UPC Number:

78620995072

Status:

Active

Description:

PMAFIX black female thread adapter with UNEF threads and O-ring. Material - polyamide 6, thread size - 1-3/4 in. -18UNS, conduit size NW - 36.

Application

For use in machine, vehicle and traction building

Characteristics

- Very high impact resistance
- Vibration proof connection to PMAFLEX conduits
- High conduit pull-out strength
- Very good chemical properties
- Self-extinguishing, free from halogens and cadmium
- Fits both conduit profiles - Fine (T) and coarse (G)

General

Material	Polyamide 6
Color	Black
Thread Type	UNEF
Compatible With	PMAFLEX, PMA Smart Line

Dimension Information

Fits to Conduit Size (NW)	36
Fits to Conduit Size (metric)	40
Fits to Conduit Size (inches)	1 1/4
Thread Length (mm)	10.0
Thread Size (UNEF)	1 3/4" - 18UNS

Technical Information

Temperature Range-Continuous (Celsius)	-40 degree C to +105 degree C
Temperature-Short-Term (Celsius)	+160 degree C
Technical Data Sheet	Available on Website
Chemical Resistance Chart	Available on Website

Specifications

3dmodel	Available on Website
---------	----------------------

IP Ratings

IP Rating	IP68 stat. / IP67 dyn.
-----------	------------------------

Packaging

T&B Inner Pack	20
Package in Units	60
T&B Sold in UOM	Each
T&B Weight Per UOM	0.15 lbs. Each

Application Support

PMA Reference Guide	Available on Website
Product Overview-PMAFIX Connectors	Available on Website
PMAFIX Connectors-Safety and Sealing Systems	Available on Website

Certifications

RoHS Compliance

Yes

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com