



Flexible Conduits & Fittings

T&B Catalog Number:

BVWD-M253GT

UPC Number:

78620995338

Status:

Active

Description:

PMAFIX 90 degree black one-piece universal elbow with universal safety clip. Material - polyamide 6, thread size - M25 x 1.5, conduit size NW - 23.

Application

In a wide range of applications where it is important that the cable protection system offers a high grade of sealing and safety.

Characteristics

- High pull-out strength values
- Vibration proof connection to PMAFLEX conduits
- Hand opening not possible
- Easy mounting, simple conduit push-in installation
- Can be re-opened with a screwdriver
- Self-extinguishing, free of halogen and cadmium and are extremely shock resistant
- Fits both conduit profiles - Fine (T) and coarse (G)

General

Material	Polyamide 6
Color	Black
Thread Type	Metric
Compatible With	PMAFLEX

Dimension Information

Fits to Conduit Size (NW)	23
Fits to Conduit Size (metric)	25
Fits to Conduit Size (inches)	3/4
Thread Size (Metric)	M25 x 1.5

Technical Information

Temperature Range-Continuous (Celsius)	-40 degree C to +105 degree C
Temperature-Short-Term (Celsius)	+160 degree C
Technical Data Sheet	Available on Website
Chemical Resistance Chart	Available on Website

Specifications

3dmodel	Available on Website
---------	----------------------

IP Ratings

IP Rating	IP66 stat. / IP54 dyn.
-----------	------------------------

Packaging

T&B Inner Pack	30
Package in Units	150
T&B Sold in UOM	Each
T&B Weight Per UOM	0.06 lbs. Each

Application Support

PMA Reference Guide	Available on Website
Product Overview-PMAFIX Connectors	Available on Website
	Available on Website

PMAFIX Connectors-Safety and Sealing
Systems

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com