



Family

Catalog Number: BVYR-292323GT
Product ID: 7TCA292000R0125
UPC Number: 78620998233
EAN Number: 07630030227653
Status: Active

VY Y Piece for IP68GT Conduit - 1x Conduit Size NW/Metric 29/32 2x Conduit Sizes NW/Metric 23/25, Color Black

North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	PMA
Type	Y-Connectors
Application	For Cable Protection Systems In a Wide Range of Applications
Standard	CSA
Size	NW23 x 2, NW 23 x 1
Material	Polyamide 6
Insulation Class	IP68GT
Color	Black
Temperature Rating	-40 Degrees C to 105 Degrees C; Short Term to 160 Degrees C

European Specifications (ETIM)

ETIM	EC001172 Coupler for corrugated plastic hoses
Material	Plastic
Material quality	Polyamide (PA)
Operating temperature	-40 - +105°C
Degree of protection (IP)	Other
Model	Y-piece
Nominal size	25-32mm
Colour	Black

Packaging

Inner Quantity	10
Inner Dimensions (inches)	15.35x2.8x1.9
Outer Quantity	40
Outer Dimensions (inches)	15.748x11.811x8.661
Weight Uom	7.14 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet Canada Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com