



Actual

Catalog Number: C77M
Product ID: 7TAI029550R0041
UPC Number: 78621086054
Status: Active

Non-Insulated Ring Terminal, Length .82 Inches, Width .31 Inches, Bolt Hole #8, Wire Range #12-#10 AWG, Copper, Tin Plated, On Mylar Tape, 500 Pack

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Non-Insulated Ring Terminal, Length .82 Inches, Width .31 Inches, Bolt Hole #10, Wire Range #12-#10 AWG, Copper, Tin Plated, On Mylar Tape, 500 Pack
Standard	UL E9809
Wire Size	12-10 AWG
Material	Copper

European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	None
Reel packaging	Y
AWG-range	12-10
Material	Copper
Surface protection	Tinned

Packaging

Inner Quantity	1000
Inner Dimensions (inches)	15.5x2.5x15.2
Outer Quantity	5000
Outer Dimensions (inches)	16x15.5x12.7
Weight Uom	3.13 lbs. per 1000

Documents / Support Tools

Technical Data Sheet CA	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com