



Actual

**Catalog Number:** C108-90-AS4  
**Product ID:** 7TCA298010R0154  
**EAN Number:** 05020963023224  
**Status:** Active

Hinged Connector Interface Fitting, 90 Degree Elbow with 360 Degree Swivel, 4-Way AS-AMP Superseal Connector to Conduit, Conduit Size NC08/NW7.5, Operating Temperature -40 to 120 Degrees Celsius, RoHS Compliant, IP40 Rating, Very High UV Protection, Polyamide (Nylon), Black

### North American Specifications (UNSPSC)

UNSPSC	39121421 Electrical connector assembly
IGCC	4586 Electrical connector assembly
Brand Name	Harnessflex
Type	Hinged AS-AMP Superseal Connector to Conduit
Special Features	High Pull-Off Strength
Application	Provide Connection Between Connector Interface and Conduit
Standard	RoHS Compliant
Size	Conduit Size NC08/NW7.5
Connection	90 Degree Elbow with 360 Degree Swivel, 4-Way Connection
Material	Polyamide/Nylon
Color	Black
Insulation	IP40
Temperature Rating	-40 to 120 Degrees C
Environmental Conditions	Very High UV Protection

### Packaging

Outer Quantity	500
Outer Dimensions (inches)	1x1x1
Weight Uom	1.3 lbs. per 100

### Header

3D Model	Available on Website
----------	----------------------

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)