



Actual

Catalog Number: C112-90-AM3
Product ID: 7TCA298010R0243
EAN Number: 05020963023279
Status: Active

Hinged Connector Interface Fitting, 90 Degree Elbow with 360 Degree Swivel, 3-Way AMP Junior or Mini Timer Connector to Conduit, Conduit Size NC12/NW10, Operating Temperature -40 to 120 Degrees Celsius, RoHS Compliant, IP40 Rating, Very High UV Protection, Polyamide (Nylon), Black

North American Specifications (UNSPSC)

| | |
|--------------------------|--|
| UNSPSC | 39121421 Electrical connector assembly |
| IGCC | 4586 Electrical connector assembly |
| Brand Name | Harnessflex |
| Type | Hinged AMP Junior or Mini Timer Connector to Conduit |
| Special Features | High Pull-Off Strength |
| Application | Provide Connection Between Connector Interface and Conduit |
| Standard | RoHS Compliant |
| Size | Conduit Size NC12/NW10 |
| Connection | 90 Degree Elbow with 360 Degree Swivel, 3-Way Connection |
| Material | Polyamide/Nylon |
| Color | Black |
| Insulation | IP40 |
| Temperature Rating | -40 to 120 Degrees C |
| Environmental Conditions | Very High UV Protection |

Packaging

| | |
|---------------------------|----------------|
| Outer Quantity | 500 |
| Outer Dimensions (inches) | 1x1x1 |
| Weight Uom | 0.01 lbs. Each |

Header

| | |
|----------|----------------------|
| 3D Model | Available on Website |
|----------|----------------------|

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com