



Riser-Gard Flexible Raceway

T&B Catalog Number:

DH4X1C-150

UPC Number:

79120720353

Status:

Active

Description:

1-1/2 Inch Riser-Gard? orange corrugated non-metallic flexible raceway with tape, coil length-150 foot.

Features

UL Listed and is available with tape pre-installed.

Listed to UL 2024 in accordance with the National Electrical Code per Articles 725, 770, 800 and 820 for Riser, General Purpose and other cabling optical fiber/telecommunication applications.

FT-4 Rated

Application

Riser-Gard is suitable for use in vertical runs in a shaft or between floors, as well as areas other than the plenum.

Riser and general purpose applications

General

Material	Non-Metallic
Color	Orange
Reel Length (feet)	150
Storage Temperatures	-4 degree F to 158 degree F
Handling Temperatures	-4 degree to 104 degree F
Pull Tape (lbs)	900

Dimension Information

Size (inches)	1 1/2
Coil Length (feet)	150
Minimum Bend Radius (inches)	10
Minimum O.D. (inches)	1.88
Maximum O. D. (inches)	1.93

Packaging

T&B Order Multiple	150
Package in Units	150
T&B Sold in UOM	Feet
T&B Weight Per UOM	0.22 lbs. Each

Application Support

T&B Sales Drawings	wsd-ac04182
--------------------	-------------

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E 13938

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com