



Rigid Non-Metallic Conduit Bodies & Covers T&B Catalog Number:

UPC Number: E983F
Status: 03448106603
Description: Active

1 inch Rigid non-metallic Type T conduit body.

Features

Textured lids
 Foam-in-place gasket

Application

For use with rigid/IMC conduit

General

Trade Size (inches) 1
 Material Non-Metallic
 Volume (cu.in.) 12
 Conduit Body Shape T

Dimension Information

C (inches) 29/32
 H (inches) 1 25/32
 L1 (inches) 6 7/8
 L2 (inches) 5 9/32
 L3 (inches) 4 7/16
 Q (inches) 1 3/4
 W (inches) 2 1/32

Packaging

T&B Order Multiple 20
 Package in Units 20
 T&B Sold in UOM Each
 T&B Weight Per UOM 35 lbs. per 100

Application Support

T&B Sales Drawings wsd-ac04549
 Rigid Non-metallic Conduit Bodies Available on Website
 Specifications & Applications Available on Website

Certifications



File Nbr:
 E 42728

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com