



Ferrule
T&B Catalog Number:

F9002
78621033576
Active

UPC Number:
Status:
Description:

Non-Insulated Ferrule, Length .394 Inches/10mm, Inner Diameter .039 Inches/1.0mm, Outer Diameter .083 Inches/2.1mm, Conductor Size 22 AWG/.5mm, Copper, Tin Plated

Features

Ferrules ensure reliable electrical connections when terminating conductors in screw clamp terminal blocks.



General

Ferrule Type	Uninsulated
Insulation Type	Non-Insulated
Material	Copper
Finish	Electro -Tin Plated
Color	Metallic
Wire Range	22
Wire Size (mm ²)	.50

Dimension Information

A (mm)	10.0
Diameter C (inches)	.039
Diameter C (mm)	1.0
Diameter D (inches)	.083
Diameter D (mm)	2.1
E (mm)	.15
A (inches)	.394
E (inches)	.006

Specifications

Temperature Rating	150°C
Flammability Rating	UL 94 V-0

Tooling

Tool Charts	Available on Website
Application Tools	T1, T3, ERG4
Recommended Tool	T1, T3, ERG4

Packaging

T&B Order Multiple	1000
T&B Inner Pack	1000
Package in Units	20000
T&B Sold in UOM	Each
T&B Weight Per UOM	0.63 lbs. per 1000

Application Support

T&B Sales Drawings	wsd-000319
Overview	Available on Website
Wire Guide Tables	Available on Website

Notes

Ferrule dimensions conform to DIN 46228, Part 4.

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com