



Ferrule
T&B Catalog Number:

F9027
78621033605
Active

UPC Number:
Status:
Description:

Non-Insulated Ferrule, Length .709 Inches/18mm, Inner Diameter .228 Inches/5.8mm, Outer Diameter .295 Inches/7.5mm, Conductor Size 6 AWG/16mm, Copper, Tin Plated

Features

Ferrules ensure reliable electrical connections when terminating conductors in screw clamp terminal blocks.



General

Ferrule Type	Uninsulated
Insulation Type	Non-Insulated
Material	Copper
Finish	Electro -Tin Plated
Color	Metallic
Wire Range	6
Wire Size (mm ²)	16.00

Dimension Information

A (mm)	18.0
Diameter C (inches)	.228
Diameter C (mm)	5.8
Diameter D (inches)	.295
Diameter D (mm)	7.5
E (mm)	.20
A (inches)	.709
E (inches)	.008

Specifications

Temperature Rating	150°C
Flammability Rating	UL 94 V-0

Tooling

Tool Charts	Available on Website
Application Tools	T3, ERG4
Recommended Tool	ERG4

Packaging

T&B Order Multiple	250
T&B Inner Pack	250
Package in Units	2500
T&B Sold in UOM	Each
T&B Weight Per UOM	0.63 lbs. per 1000

Application Support

T&B Sales Drawings	wsd-000319
US Cutsheet PDF Catalog Link	Available on Website
Overview	Available on Website
Wire Guide Tables	Available on Website

Notes

Ferrule dimensions conform to DIN 46228, Part 4.

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com