



Representative

Catalog Number: FBB6-1
Product ID: 7TAA014910R0056
UPC Number: 78378640232
Status: Active

Flexible Braids for Grounding, 24000 Circular Mil Area, Bolt Hole 1/4, 6 inch length, Number of Braids in Ferrule 1, 1 Bolt Hole in Ferrule

North American Specifications (UNSPSC)

UNSPSC	39121465 Flexible braid
IGCC	4695 Flexible braid
Brand Name	Blackburn
Type	Flexible Braid
Special Features	Tin-Plated Copper Braids and Ferrules for High Conductivity and Corrosion Resistance. Enables Linear Expansion, Equipment Vibration and Offset Connections.
Application	Flexible Copper Braids for use in Substation and Grounding Applications
Standard	UL E3060, CSA LR29625
Conductor Material	Tin-Plated Copper
Nominal Cross Section Conductor	24000 Circular Mills
Cable Width	.625 inch
Cable Length	6 inch
Conductor Category	Flexible
Shape Of Conductor	Flat

European Specifications (ETIM)

ETIM	EC000839 Braid wire
Conductor material	Cu, tinned
Conductor category	Class 5 = flexible
Shape of conductor	Flat
Cable height approx.	154mm

Packaging

Outer Quantity	100
Outer Dimensions (inches)	14.125x5.125x6
Weight Uom	6.5 lbs. Each

Documents / Support Tools

Technical Data Sheet CA	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com