

Catalog Number: LU57
Product ID: 7TAD013830R0010
UPC Number: 78620991242
Status: Active

1-1/2 Inch Form 7 (LU) Conduit Elbow for Use with Rigid/IMC Conduit

- BlueKote Teflon based internal finish provides a slick, easy-glide internal surface which significantly lowers the amount of force necessary to pull wires.
- Eliminates rough internal surfaces that can cut into cable jacket, insulation and conductors during pulling and also reduces installation time and risk of installer strain.
- Triple-layer protection...including two layers of epoxy coating which stops corrosion in its tracks.



Actual



Representative

Header

3D Model Available on Website

North American Specifications (UNSPSC)

UNSPSC	39131708 Electrical conduit fitting body
IGCC	5563 Electrical conduit fitting body
Brand Name	T&B
Type	Form 7 Conduit Body
Special Features	Tapered NPT Threads and Integral Bushings to Protect Wire Insulation
Application	Connect Conduit Sections, Provide Easy Access to Conductors for Maintenance and Future System Changes
Standard	UL E2969, CSA
Hub Size	1-1/2 Inch
Form	7
Material	Iron
Finish	Zinc-Plating with Acrylic Coating

Packaging

Inner Quantity	2
Inner Dimensions (inches)	8.7x3.1x9.1
Outer Quantity	10
Outer Dimensions (inches)	17x9.5x9.5
Weight Uom	3.99 lbs. Each

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000475

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com