

PRODUCT-DETAILS

RK9731

INS NYL RING TERM, 2/0AN, 3/8, YELL



General Information

Extended Product Type	RK9731
Product ID	7TAI029860R0105
EAN	5414363160335
Catalog Description	INS NYL RING TERM, 2/0AN, 3/8, YELL
Long Description	Nylon Insulated Large Ring Terminal, Length 2.52 Inches, Width .93 Inches, Maximum Insulation .610, Bolt Hole 3/8 Inch, Wire Range 2/0AN, Color Yellow, Copper, Tin Plated

Ordering

EAN	5414363160335
UPC	786210821443
Country of Origin	Mexico (MX)
Customs Tariff Number	8536904000
Selling Unit of Measure	each

Container Information

Package Level 1 Units	25 piece
Package Level 1 Width	4 in 102 mm
Package Level 1 Height	3 in 76 mm
Package Level 1 Depth / Length	4 in 102 mm

Package Level 2 Units	250 piece
Package Level 2 Width	8.9 in 226 mm
Package Level 2 Height	3.9 in 99 mm
Package Level 2 Depth / Length	21.4 in 544 mm

Additional Information

Application	UL Listed and CSA Certified
Brand / Label	Sta-Kon
Color	Yellow
Effective Date	19680527
Material	Copper
Product Name	ELECTRICAL TERMINAL
Product Type	Nylon Insulated Ring Terminal
Special Functions	Funneled Barrel Entry, Deep Internal Serrations, Brazed or overlapping seams.
Standards	UL E9809
Voltage Rating	600 V
Wire Size	2/OAN

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	RK9731
Instructions and Manuals	RK9731

Classifications

ETIM 6	EC001052 - Solderless copper terminals for copper conductors
ETIM 7	EC001052 - Solderless copper terminals for copper conductors
ETIM 8	EC001052 - Solderless copper terminals for copper conductors
UNSPSC	39121432
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4603 >> Electrical terminals

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Compression & Mechanical Connectors

