


NOTES:

1. MATERIAL: MODIFIED PPE, HALOGEN FREE, COLOR- WHITE
2. TEMPERATURE RATING: -40°F [-40°C] TO 203°F [95°C]
3. FLAMMABILITY RATING: UL94V-1
4. FLUSH MOUNT DESIGN. COVER SITS FLUSH WITH SIDE WALLS OF DUCT
5. "NO-SLIP" FRICTION BEAD INTERLOCKS WITH DUCT SIDE WALLS TO PREVENT VIBRATION SLIPPAGE

CATALOG NO.	SIZE	A (WIDTH)
TY1CHW6	1"	1.250 [31,75]
TY15CHW6	1-1/2"	1.750 [44,45]
TY2CHW6	2"	2.250 [57,15]
TY3CHW6	3"	3.250 [82,55]
TY4CHW6	4"	4.250 [107,95]

GENERAL NOTES

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
2. DIMENSIONS IN BRACKETS [] ARE IN METRIC UNITS.

REVISIONS

- SEE ERN ***** FOR APPROVAL SIGNATURES & RELEASE DATE.
PROJECT NO: *****

DESCRIPTION: **WIRING DUCT COVER
HALOGEN FREE**

ORIGINAL PROJECT NO / (ERN NO)

FD55656 / 2006987

SHEET NO:

1 OF 1

DRAWING NO:

WSD-000284

Thomas & Betts
www.tnb.com