

Catalog Number: TYS24-280
Product ID: 7TAG009460R0117
UPC Number: 78621091547
EAN Number: 05414363067900
Status: A



Multi-Lok 316 Stainless Steel Cable Tie, Uncoated, Length of 610mm (24 Inches), Width of 7mm (0.28 Inch), Thickness of 0.25mm (0.01 Inch), Tensile Strength Rating of 1112 Newtons (250 Pounds)

- Application Tools: WTAE200, WTAE201,

Actual

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5046 Stainless Steel Ties
Type	Stainless Steel
Standard	UL E49405
Width	0.28 in ; 7 mm
Length	24 in ; 610 mm
Thickness	0.01 in ; 0.25 mm
Bundle Diameter	Max 7.5 in ; Max 190 mm
Material	316 Stainless Steel
Color	Metallic Gray
Lock Mechanism	Multi-Lok
Tensile Strength	250 pounds ; 1112 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	7mm
Length belt/tape/tie	610mm
Tie thickness	0.25mm
Max. bundle diameter	190mm
Min. holding force	1112N
Operating temperature	-40-+150°C
Model	Internal toothing
Band closure	Ball latch
Material	Metal
Material quality	Stainless steel 316 (V4A)
Surface protection	Untreated
Halogen free	N
Colour	Stainless steel
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N
UL approval	Y

Packaging

Inner Quantity	100
Outer Quantity	1000
Outer Dimensions (inches)	31.6x9.2x10
Weight Uom	1.98 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000433
Catalog Page	Available on Website

For further technical assistance, please contact us...

ABB Installation Products - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com