



Actual

Catalog Number: XC291
Product ID: 7TAA010560R0023
UPC Number: 78599144716
EAN Number: 05414363165378
Status: A

Connector, Non-Insulated 90 Degree Clamp-Type, Size 1/2 Inch, Clamping Range 0.65 Inch - 1.00 Inch, Length 2.08 Inch, Die Cast Zinc

North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Brand Name	Steel City
Type	Armored Cable/Flexible Metal Conduit Fittings
Special Features	Captive two screw
Standard	UL e1383
Size	1/2 Inch
Material	Zinc Die Cast

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1/2 inch
Model	90°-Bend
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
One-piece	Y
Material housing	Zinc die-cast
Surface protection	Untreated
Approved in combination with protective conduit DIN EN 61386-23	N
Approved in combination with protective conduit FI	N

Packaging

Inner Quantity	25
Inner Dimensions (inches)	7.4x5.3x3.6
Outer Quantity	250
Outer Dimensions (inches)	19x11.2x8.2
Weight Uom	16.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website

For further technical assistance, please contact us...

ABB Installation Products - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com