



AST | AST4300

TE Internal #: 11105596-00

Industrial Pressure Transducer, Gauge, 4 – 20 mA Output Signal, 2X, Min Proof Pressure Range, AST4300

[View on TE.com >](#)

Sensors > Pressure Sensors > Pressure Transducers > Non-Incendive Pressure Transducer



Pressure Sensor Type: **Industrial Pressure Transducer**

Pressure Type: **Gauge**

Hazardous Area Approval: **Non-Incendive**

Output Signal Type: **4 – 20 mA**

Pressure: **20 bar [290 psi]**

[All Non-Incendive Pressure Transducer \(103\)](#)

Features

Product Type Features

Pressure Sensor Type	Industrial Pressure Transducer
Pressure Type	Gauge

Configuration Features

Electrical Connection	Conduit 10 ft
-----------------------	---------------

Electrical Characteristics

Supply Voltage Range	10 – 28 V
----------------------	-----------

Body Features

Port Material	316L
---------------	------

Usage Conditions

Pressure	20 bar[290 psi]
Operating Temperature Range	-40 – 80 °C[-40 – 176 °F]

Operation/Application

Output Signal Type	4 – 20 mA
Proof Pressure Range	2X, Min
Pressure Accuracy	±0.25% FSO

Industry Standards



Compatible With Agency/Standards Products	UL
Hazardous Area Approval	Non-Incendive

Other

Sensor Options	No Option
Port Fitting	1/4 MNPT

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量超出标准 Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) SVHC > Threshold: 2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one (3.9% in 17980139677) Pb (80.3% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-PTT0043
Non-Incendive Pressure Transducer

Also in the Series | AST4300



Industrial Pressure Transducers(103)



Pressure Transducers(103)

Customers Also Bought



TE Part #NB-PTCO-159
Pt100, 2.0x2.3, Class C, PTFC101C1A0




TE Part #86-100G-R
100 PSIG RIBBON CABLE MV PRESSURE SENSOR



TE Part #CJ1465-000
55AC8113-22-9/96-9-9CS2275



TE Part #NB-PTCO-163
Pt1000, 2.0x2.3, Class C, PTFC102C1A0



TE Part #132005-1
STRATO-THERM, HR, FLAG, 12-10, M4 (#8)



TE Part #1-1625893-4
5W SM M/OX 2% 27R



TE Part #7-1879350-5
RR01 5% 270R AMMO



TE Part #4-1879355-9
RR03 5% 430K AMMO



TE Part #1-1879447-8
TE 200W 27R 5% Bracket



TE Part #2-2329383-5
PB ON/OFF FC BLU M1 TERM IP68



Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_11105596-00_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_11105596-00_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_11105596-00_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AST4300 Pressure Transducer Datasheet](#)

English