



Fiber Optic Swab

2316-2317

Precisely designed, manufactured and packaged to serve a wide variety of cleaning and maintenance needs. TechSwabs are manufactured in accordance with Techspray's rigid specifications, using specialized materials to ensure low particle generation. Cotton swabs are the most economical choice for high volume usage. Foam swabs are ideal for more precision cleaning where linting needs to be avoided.



High-precision foam swab for fiber optic connectors

Foam fiber optic swabs are ideal for removing transmission disrupting contaminants in bulkhead connectors. The head conforms to the various connector shapes, cleaning the conductor bulkhead corners inside the bulkhead pocket. Foam fiber optic swabs are an economic choice over wrapped swabs. Tips are heat bonded, so no contaminating glues have been used.

- Reticulated polyurethane foam
- Head thermally bonded
- High absorbency
- Low particulate count
- Flexible tip for softer touch
- Designed to fit standard fiber optic apertures

Product Packaging

2316-50
1.25mm Fiber Optic Swab
50 ct
12 units/case

2316-1000
1.25mm Fiber Optic Swab
1000 ct
1 units/case

2317-50
2.5mm Fiber Optic Swab
50 ct
12 units/case

2317-1000
2.5mm Fiber Optic Swab
1000 ct
1 units/case



Techspray
8125 Cobb Center Drive,
Kennesaw, GA 30152
800-858-4043 • www.techspray.com



Technical Information

Environmental Policy

Techspray is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Resources

Techspray products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: www.techspray.com.

North America

Techspray
P.O. Box 949
Amarillo, TX 79105
800-858-4043
Email: tsales@techspray.com

Europe

ITW Contamination Control
Saffierlaan 5
2132 VZ Hoofddorp
The Netherlands
+31 88 1307 400
Email: info@itw-cc.com

Countries Outside US

Call to locate a distributor in your country.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.

© 2015 Techspray, A Division of ITW