

**WIREGRIP HIGH TEMPERATURE CONNECTORS**

- Color-coded to industry standards for size selection from 22 – 14 AWG
- Square-wire spring threads provide a positive “Grip” to ensure quick and tight secure connections
- Rated at 300 or 600 volt max. for building wiring
- Tough thermoplastic, UL 94V-2 flame-retardant shell at 150°C (302°F)
- UL 486C Listed and CSA 22.2 NO. 188 Certified
- Copper to Copper connections only
- Operating temperature - 150°C (302°F)



Color	Voltage	General Wire Combination Range	Min	Max	Part Number	Quantity
Black	300V	22 - 14 AWG	1 #18 Str w/1 #22 Str	2#18 Str	CPGI-WC-HT-300-BG-1000	1000/BAG
Black	300V	22 - 14 AWG	1 #18 Str w/1 #22 Str	2#18 Str	CPGI-WC-HT-300-BULK	20,000/Cartron
Black	600V	22 - 14 AWG	1 #16 w/1#22	1 #14 w/1 #16 w/1 #18	CPGI-WC-HT-600-BG-1000	1000/BAG
Black	600V	22 - 14 AWG	1 #16 w/1#22	1 #14 w/1 #16 w/1 #18	CPGI-WC-HT-600-BULK	20,000/Cartron

**WINGGRIP CONNECTORS**



- Color-coded to industry standards for size selection from 18 – 6 AWG
- Square-wire spring threads provide a positive “Grip” to ensure quick and tight secure connections
- Specially designed wings provide the installer a secure and solid twist-on connection
- Rated at 600 volt max. for building wiring and 1000 volt max. in lighting fixtures/luminaries and signs
- Tough thermoplastic, UL 94V-2 flame-retardant shell at 105°C (221°F)
- UL 486C Listed and CSA 22.2 NO. 188 Certified
- Copper to Copper connections only
- Operating temperature - 105°C (221°F)

Color	General Wire Combination Range	Min	Max	Part Number	Quantity
Yellow	18 - 10 AWG	2 #18	3 #12 Sol	CPGI-WC-WNG-YW-CL-10	20/CLAM
Yellow	18 - 10 AWG	2 #18	3 #12 Sol	CPGI-WC-WNG-YW-BG-100	100/BAG
Yellow	18 - 10 AWG	2 #18	3 #12 Sol	CPGI-WC-WNG-YW-BG-225	225/BAG
Yellow	18 - 10 AWG	2 #18	3 #12 Sol	CPGI-WC-WNG-YW-BG-500	500/Bag
Yellow	18 - 10 AWG	2 #18	3 #12 Sol	CPGI-WC-WNG-YW-BULK	5000/Cartron
Red	18 - 8 AWG	3 #16w/1 #18	5 #12 Sol	CPGI-WC-WNG-RD-CL-8	10/CLAM
Red	18 - 8 AWG	3 #16w/1 #18	5 #12 Sol	CPGI-WC-WNG-RD-BG-100	100/BAG
Red	18 - 8 AWG	3 #16w/1 #18	5 #12 Sol	CPGI-WC-WNG-RD-JR-300	300/JAR
Red	18 - 8 AWG	3 #16w/1 #18	5 #12 Sol	CPGI-WC-WNG-RD-BG-500	500/Bag
Red	18 - 8 AWG	3 #16w/1 #18	5 #12 Sol	CPGI-WC-WNG-RD-BULK	5000/Cartron
Red/ Yellow	See Red or Yellow Wing Specs			CPGI-WC-WNG-YW/RD-BG-150	150/BAG
Blue	14 - 6 AWG	2 #10 w/1 #12	3 #8 w/1 #12	CPGI-WC-WNG-BL-CL-3	3/CLAM
Blue	14 - 6 AWG	2 #10 w/1 #12	3 #8 w/1 #12	CPGI-WC-WNG-BL-BG-50	50/BAG
Blue	14 - 6 AWG	2 #10 w/1 #12	3 #8 w/1 #12	CPGI-WC-WNG-BL-BG-100	100/Bag
Blue	14 - 6 AWG	2 #10 w/1 #12	3 #8 w/1 #12	CPGI-WC-WNG-BL-BULK	1500/Cartron