



UTILUX

TE Internal #: A37853-000

Compression Connectors, ASIA / ANZPAC, Compression, ≤ 1 kV, Copper, Hexagonal Crimping, Tinned Cu, Indoor Use, Outdoor Use, Copper Palm, Terminal Lug

[View on TE.com >](#)

Energy & Power > Power System Connectors > Compression Connectors



Compression Connector Product Availability: **ANZPAC, ASIA**

Compression Connector Technology: **Compression**

Compression Connector Voltage Class: **≤ 1 kV**

Compression Connector Conductor Material: **Copper**

Conductor Cross-Section: **630 mm<sup>2</sup>**

**Features**

**Product Type Features**

Type	Terminal Lug
Compression Connector Technology	Compression
Compression Connector Material	Tinned Cu
Underground Network Component Type	Terminal Lug

**Configuration Features**

Number of Holes	1
-----------------	---

**Electrical Characteristics**

Compression Connector Voltage Class	≤ 1 kV
-------------------------------------	--------

**Body Features**

Barrel Type	Standard
Compact Format	No
Compression Connector Conductor Material	Copper
Copper Palm	Yes

**Contact Features**

Crimp Type	Hexagonal Crimping
------------	--------------------

**Dimensions**

Lug Width	65 mm[2.559 in]
-----------	-----------------



Barrel Length	98 mm[3.858 in]
Lug Length	190 mm[7.48 in]
Barrel Diameter	33.5 mm[1.319 in]
Conductor Cross-Section	630 mm <sup>2</sup>
Compression Connector Stud Size	M12

### Operation/Application

Indoor Use	Yes
Outdoor Use	Yes

### Product Availability

Compression Connector Product Availability	ANZPAC, ASIA
--	--------------

### Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JUL 2019 (201) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



## Compatible Parts



TE Part # 2107475-2  
UNIPRESS 6/120 +COF+CHARG



TE Part # 2107725-1  
AUTOPRESS L62+ COF+CHARG




TE Part # 2107730-1  
AutoPress 80 18V+COF+CHARG



TE Part # 2107733-4  
AUTOPRESS C120 18V+COF+CHARG 110V

## Customers Also Bought



TE Part #325308  
TERMINAL,AMPOWER 1/0 0



TE Part #EN3750-775  
TCTS-3/0-1/2-U



TE Part #EN3750-799  
TCTS-500-1/2-U



TE Part #6-1393139-3  
MDR-5061=MDR

TE Part #CY6485-000  
RSTI-SY247

TE Part #CY6488-000  
RSTI-SY250

TE Part #042316-000  
EPKJ-17A/1XU-1HL

## Documents

### Product Drawings

[SEG630M12X01/1](#)

English

### Datasheets & Catalog Pages

[EPP-2487-DDS04-AU-3\\_16-SEG-UTILUX](#)

English