



6278082-2 | CONN KIT, +ST 50/125

Body Features

Body Material	Aluminum
Body Plating Material	Nickel
Boot Color	Aqua
Boot Material	PE
Boot Type	Bare buffer Long
Epoxyless	Yes
Ferrule Hole Size	128.0 μ m

Dimensions

Outside Cable Diameter (Max) 3.0 mm | 0.1 in

Mechanical Attachment

Coupling Nut Material Zinc

Packaging Features

Packaging Method Bag
Packaging Quantity 1

Product Type Features

Product Type Connector
Connector Type ST
Optical Mode Multimode
Connector Style Simplex
Fiber Type OM3
System LIGHTCRIMP PLUS
Booted Yes
Ferrule Material Ceramic
Fiber Diameter 50/125 μ m
Pre-Polished No

Signal Characteristics

Insertion Loss (Max) 0.30 dB

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant