



### Main

Range	ClimaSys
Product	ClimaSys CA
Application	Outdoor heavy duty
Range compatibility	ClimaSys (ClimaSys CV) fan Spacial (Spacial SFHD) Spacial (Spacial S3HD) Thalassa (Thalassa PHD)
Certification	UL conforming to UL 94 CE conforming to ENV 1630
Product or component type	Outlet grille
Accessory / separate part category	Thermal management accessory
Accessory / separate part destination	ClimaSys ventilation system
Mounting location	Sides of enclosure
Mounting position	Vertical
Fixing mode	By screws
Device composition	1 support frame 1 external part 4 screw 1 G3 M1 synthetic standard filter

### Complementary

Material	Steel Polyamide 6 Stainless steel
Colour	External part: grey (RAL 7035) Internal part: green (Pantone 355C)
Surface finish	Epoxy-polyester powder
Cut-out dimensions	223 x 223 mm
Height	315 mm external:
Width	300 mm external:
Depth	60 mm external:
IP degree of protection	IP55 ( outdoor )

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	31.0 cm
Package 1 Length	35.0 cm
Package 1 Weight	3.042 kg
Unit Type of Package 2	PAM
Number of Units in Package 2	48
Package 2 Height	59.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	157.0 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 Monate
----------	-----------