



Main

Range	ClimaSys
Product name	ClimaSys CR
Product or component type	Resistance heater with fan
Power range	200 W
Input voltage	230 V AC 50/60 Hz

Complementary

Operating position	Vertical
Ambient air temperature for operation	-40...70 °C
IP degree of protection	IP20
Product certifications	UL VDE
Material	Body: extruded aluminium
Height	140 mm
Width	80 mm
Depth	20 mm
Condition of use	Electrical protection is needed Heaters must be installed with a thermal controller Air sealed enclosure
Fixing mode	By clips
Mounting support	35 mm DIN rail

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2 cm
Package 1 Width	8 cm
Package 1 Length	14 cm
Package 1 Weight	924 g
Unit Type of Package 2	CAR
Number of Units in Package 2	20
Package 2 Height	31 cm
Package 2 Width	39.5 cm
Package 2 Length	59.5 cm
Package 2 Weight	19.822 kg
Unit Type of Package 3	PAM
Number of Units in Package 3	400
Package 3 Height	140 cm
Package 3 Width	100 cm
Package 3 Length	120 cm
Package 3 Weight	409.44 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------